


General Information

| | |
|---------------|--|
| Series | AFPI 160 |
| Style | Feed-Through Filter |
| Description | Small Signal Feed-Through Filters |
| Features | Military, Industrial, Medical, Telecom |
| RoHS | Yes |
| Lead | Fast On |
| Terminal Type | Faston |

[Click here](#) for the 3D model.

| Dimensions | |
|------------|----------|
| D | 16mm MIN |
| Lead | Fast On |
| A | 16mm MIN |
| B | 38mm MIN |
| D1 | 1.2 |

| Packaging Specifications | |
|--------------------------|------|
| Packaging | Bulk |
| Packaging Quantity | 1 |

| Specifications | |
|-------------------|-----------|
| Voltage AC | 50 VAC |
| Voltage DC | 100 VDC |
| Rated Current | 16 A |
| Ripple Current | 16 A |
| Rated Temperature | 40°C |
| Temperature Range | -25/+85°C |
| Climate Category | 25/085/21 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.