



Click [here](#) for the 3D model.

General Information

Series	AKCL 100
Style	Feed-Through Filter
Description	Signal Feed-Through Filters
Features	Military, Industrial, Medical, Telecom
RoHS	Yes
SCIP Number	96b8932c-2923-4b10-a6a1-01b5987a0a00
Lead	Wire Leads
Terminal Type	Wire

Dimensions

D	10mm MAX
L	27mm MAX
L1	14.7mm MAX
L2	4.85mm MAX
K	17.2mm MAX
Lead	Wire Leads
F	1.5mm NOM

Specifications

Voltage AC	50 VAC
Voltage DC	80 VDC
Rated Current	10 A
Ripple Current	10 A
Rated Temperature	40°C
Temperature Range	-55/+125°C
Climate Category	55/125/56
DC Resistance	0.01 mOhms

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.