


## ALC10S1104DL

ALC10S, Aluminum, Aluminum Electrolytic, 10,000 uF, 20%, 80 VDC, -40/+85°C, 10 mm



Click [here](#) for the 3D model.

General Information	
Series	ALC10S
Dielectric	Aluminum Electrolytic
Description	Audio Grade Snap-In
Features	Audio Grade
RoHS	Yes
Lead	2 Pin
Typical Component Weight	105 g
Notes	Dimensions Include Slewing.
Shelf Life	156 Weeks

Dimensions	
D	35mm NOM
L	80mm NOM
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Specifications	
Capacitance	10,000 uF
Tolerance	20%
Voltage DC	80 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	15000 Hrs
Leakage Current	4800 uA (5min 20°C)

Packaging Specifications	
Slewing	Yes
Packaging	Tray

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.