



Click [here](#) for the 3D model.

#### General Information

Series	BEAD L
Style	Through-Hole
RoHS	Yes

#### Dimensions

D	2.4mm MAX
L	8.5mm MAX
W	8mm MAX
LL	15mm MIN
S	5mm NOM
F	0.65mm NOM

#### Packaging Specifications

Packaging	T&R
Packaging Quantity	2000
Typical Component Weight	300 mg

#### Specifications

Temperature Range	-20/+70°C
-------------------	-----------