
B-13

Aliases (UDLB0001300000)

Differential Mode Chokes - Signal, KEMET, BEAD W, Through-Hole, Normal Mode



Click here for the 3D model.

General Information	
Series	BEAD W
Style	Through-Hole
RoHS	Yes

Dimensions	
L	7mm MAX
W	8mm MAX
LL	5mm +/-2mm
Wire Size	0.4mm
F	0.4mm NOM

Specifications	
Temperature Range	-20/+65°C

Packaging Specifications	
Packaging	Bulk
Packaging Quantity	4000
Typical Component Weight	500 mg

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO