



Click [here](#) for the 3D model.

**General Information**

Series	C4BS
Dielectric	Metallized Polypropylene
Style	Radial
Features	IGBT Circuit
RoHS	Yes
Lead	Flat Tabs
Typical Component Weight	61.67 g
Miscellaneous	KEMET Style B Tabs.

**Dimensions**

L	41.5mm +1.5/-0.7mm
H	40mm +0.2/-0.7mm
T	20mm +0.4/-0.7mm
S	22mm +/-0.2mm
S1	16mm +/-0.2mm
S2	28mm +/-0.2mm
P	6mm NOM

**Packaging Specifications**

Packaging	Bulk, Bag
Packaging Quantity	48

**Specifications**

Capacitance	1 uF
Tolerance	5%
Voltage DC	1000 VDC
Voltage AC	600 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Max dV/dt	827 V/us
ESR	3.7 mOhms (100kHz)
Ripple Current	23 Amps (100kHz 70C), 827 Amps (Peak)
Inductance	41 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.