
ESD-R-12M-H

Aliases (UECESDR12MH000)

EMI Suppression, KEMET, ESD-R-H, Round - Toroidal, Noise Suppression



Click here for the 3D model.

General Information	
Series	ESD-R-H
Style	Round - Toroidal
Cable Type	Round Cable
Description	EMI Core Solid, For Round Cables, Toroidal Cores
Features	High Heat Resistance, Cable Holding Mechanism
RoHS	Yes
Qualifications	UL94V-0
Case Color	White
Materials	Mn-Zn
Core	Mn-Zn Ferrite

Dimensions	
D	15mm MAX
D2	5mm +/-1.0mm
T	9mm MAX

Specifications	
Temperature Range	-40/+120°C
Effective Frequency	10 MHz (AM Band Range)

Packaging Specifications	
Packaging	Tray, Box
Packaging Quantity	2000
Typical Component Weight	2.6 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO