



Click [here](#) for the 3D model.

General Information

Series	ESD-R-B
Style	Round - Snail
Cable Type	Round Cable
Description	EMI Core Solid, For Round Cables, Toroidal Cores
Features	Snail Shaped Case
RoHS	Yes
Qualifications	UL94 V-2
Case Color	White
Toroidal	ESD-R-38D
Materials	Mn-Zn
Core	Mn-Zn Ferrite

Specifications

Temperature Range	-25/+60°C
Effective Frequency	10 MHz (AM Band Range)

Dimensions	
D	42.4mm +/-0.8mm
D2	17.9mm +/-0.8mm
L	28mm +/-0.8mm
T	16mm MAX

Packaging Specifications	
Packaging	Tray, Box
Packaging Quantity	240
Typical Component Weight	58.6 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.