



Click [here](#) for the 3D model.

**General Information**

Series	ESD-R
Style	Round - Toroidal
Cable Type	Round Cable
Description	EMI Core Solid, For Round Cables, Toroidal Cores, Coated Type
RoHS	Yes
Qualifications	UL94 V-2
Case Color	Green

**Dimensions**

D	59mm MAX
D2	34mm MIN
T	21mm MAX

**Packaging Specifications**

Packaging	Tray, Box
Packaging Quantity	60
Typical Component Weight	140.9 g

**Specifications**

Temperature Range	-25/+85°C
Effective Frequency	500 MHz (FM Band Range)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.