



**General Information**

Series	ESTX
Style	Tape
Description	Flex Suppressor Halogen Free Type
Features	Resonance suppression
RoHS	Yes
Qualifications	UL94 HB, UL File No. E176124
Environment	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

**Dimensions**

L	10000mm NOM
W	9mm NOM
T	0.05mm NOM

**Packaging Specifications**

Adhesive Thickness	0.03 mm
Typical Component Weight	25 g

**Specifications**

Temperature Range	-40/+105°C
Permeability	150 u At 3MHz
Effective Frequency	1 MHz to 3GHz
Specific Gravity	3.3 TYP
Surface Resistivity	1 MOhm/sq. TYP

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.