



Click [here](#) for the 3D model.

General Information

Series	FLLE2-R
Style	Chassis Mount
Description	Single Phase, Chassis Mount Filters
Features	Single Phase
Phase	Single-phase
RoHS	Yes
Qualifications	IEC/EN 60939, UL, CSA
Lead	Threaded Studs M4
Terminal Type	Threaded Studs M4
Test Voltage DC (P to N)	1300 VDC

Dimensions

L	91mm MIN	Voltage AC	300 VAC
W	51mm MIN	Voltage DC	300 VDC
H	45mm MIN	Inductance	0.8 mH
Lead	Threaded Studs M4	Rated Frequency	50-60 Hz
		Rated Current	20 A

Packaging Specifications

Packaging	Bulk	Voltage AC	300 VAC
Packaging Quantity	1	Voltage DC	300 VDC
Typical Component Weight	350 g	Inductance	0.8 mH
		Rated Frequency	50-60 Hz
		Rated Current	20 A
		Ripple Current	20 A
		Rated Temperature	40°C
		Temperature Range	-25/+100°C
		Climate Category	25/100/21
		Leakage Current	0.37 mA
		Test Voltage DC (P/N to E)	2250 VDC

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.