




General Information	
Supplier	YAGEO
Series	HHV
Style	Axial
Description	Metal glazed film resistors, high-voltage & high ohmic
RoHS	Yes
AEC-Q200	No

Dimensions

Packaging Specifications

Packaging	T&R
Packaging Quantity	2500

Specifications

Resistance	10 MOhms
Resistance Tolerance	1%
Power	0.5 W (70C)
Temp. Coefficient	-/+200 ppm/C
Temperature Range	-55/+155°C

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.