



Click [here](#) for the 3D model.

#### General Information

Series	KHC DISC Comm SL HV
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Wire Leads
Failure Rate	N/A

#### Dimensions

D	7.5mm MAX
T	4.5mm MAX
S	5mm NOM
LL	25mm +/-1mm
F	0.6mm +/-0.1mm

#### Specifications

Capacitance	150 pF
Tolerance	10%
Voltage DC	1000 VDC
Temperature Range	-25/+85°C
Temp. Coefficient	SL

#### Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------