


General Information

Series	MA
Style	Plastic Box
Description	Noise Filters
RoHS	Yes
Qualifications	UL, CSA, TUV
Miscellaneous	30 K Self-Temperature Rise Max.

[Click here for the 3D model.](#)
Dimensions

L	38mm NOM	Voltage AC	250 VAC
W	30mm NOM	Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
H	22.5mm NOM	Rated Current	2 A (AC/DC)

Packaging Specifications

Packaging	Tray, Box	Ripple Current	2 A (AC/DC)
Packaging Quantity	50	Temperature Range	-25/+55°C
Typical Component Weight	30 g	Leakage Current	0.75 mA

ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground
-----	--------------------------------------------------------

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.