
MA-2043

Aliases (UNFMA2043XXXXX)

Obsolete

EMI Filters, KEMET, MA, Plastic Box, Noise Suppression



Click here for the 3D model.

General Information	
Series	MA
Style	Plastic Box
Description	Noise Filters
RoHS	Yes
Qualifications	UL, CSA, TUV
Notes	Last time buy due: May 31, 2024.
Miscellaneous	30 K Self-Temperature Rise Max.

Dimensions	
L	38mm NOM
W	30mm NOM
H	22.5mm NOM
LL	7mm MIN

Packaging Specifications	
Packaging	Tray, Box
Packaging Quantity	50
Typical Component Weight	30 g

Specifications	
Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	4 A (AC/DC)
Ripple Current	4 A (AC/DC)
Temperature Range	-25/+55°C
Leakage Current	0.75 mA
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO