



Click [here](#) for the 3D model.

#### General Information

Series	MR
Type	Current
Style	Round - Toroidal
Description	Zero-Phase Current Transformers
Features	High Sensitivity, Compact
Lead	2 Pin
RoHS	Yes
REACH	Yes
Notes	Measurement Conditions: f=60Hz, R=1000 Ohms, Io=15 mAmps

#### Dimensions

D	6mm MIN
H	7.9mm MAX
D2	17.5mm MAX
D3	19mm MAX

#### Specifications

Temperature Range	-20/+80°C
Voltage DC	12.5 mV MIN (Output)
Current	15 Amps
ESR	30 Ohms
Miscellaneous	Overinput characteristics (After DC5A input) = 10% MAX.

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	960
Typical Component Weight	2.7 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.