



Click [here](#) for the 3D model.

General Information

Series	PMZ2035/P435
Dielectric	Metallized Paper
Style	Radial
Features	RC Unit approved
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Qualifications	ENEC
Construction	Molded
Typical Component Weight	10 g
Miscellaneous	Resistor Tolerance: +/-30%. Resistor= 150 Ohms.

Specifications

Capacitance	0.1 uF
Tolerance	10%
Voltage DC	1000 VDC
Voltage AC	440 VAC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Insulation Resistance	6 GOhms
Safety Class	X1

Dimensions

L	30.5mm MAX
H	19mm MAX
T	12.1mm MAX
S	25.4mm +/-0.4mm
LL	6mm -1mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	800