
RC0100FR-0722K1P

Aliases (RC0100FR0722K1P)

YAGEO, RC_P, Thick Film, SMD Chip, 22.1 kOhms, 1%, 01005 / 0402



Click here for the 3D model.

General Information	
Supplier	YAGEO
Series	RC_P
Style	SMD Chip
Description	Lead-Free Thick Film Chip Resistors
RoHS	Yes
Termination	Tin
Case Code (EIA / mm)	01005 / 0402

Dimensions	
L	0.4mm +/-0.02mm
W	0.2mm +/-0.02mm
T	0.13mm +/-0.02mm
B1	0.1mm +/-0.03mm
B2	0.1mm +/-0.03mm

Packaging Specifications	
Packaging	T&R, 178mm

Specifications	
Resistance	22.1 kOhms
Resistance Tolerance	1%
Power	0.03 W (70C)
Temp. Coefficient	-/+200 ppm/C
Temperature Range	-55/+125°C
Voltage DC	15 V (Max Continuous Voltage at Full Rated Power), 30 Max Over Voltage, 30 Dielectric Withstanding Voltage

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO