



Click [here](#) for the 3D model.

### General Information

|                      |                               |
|----------------------|-------------------------------|
| Supplier             | YAGEO                         |
| Series               | RC                            |
| Style                | SMD Chip                      |
| Description          | Standard Jumper Chip Resister |
| RoHS                 | Yes                           |
| Termination          | Tin                           |
| Shelf Life           | 104 Weeks                     |
| Case Code (EIA / mm) | 1210 / 3225                   |

### Specifications

|                      |                                                                                                               |
|----------------------|---------------------------------------------------------------------------------------------------------------|
| Resistance           | 62 Ohms                                                                                                       |
| Resistance Tolerance | 5%                                                                                                            |
| Power                | 0.5 W (70C)                                                                                                   |
| Temp. Coefficient    | -/+100 ppm/C                                                                                                  |
| Temperature Range    | -55/+155°C                                                                                                    |
| Voltage DC           | 200 V (Max Continuous Voltage at Full Rated Power), 500 Max Over Voltage, 500 Dielectric Withstanding Voltage |

### Dimensions

|    |                  |
|----|------------------|
| L  | 3.1mm +/-0.1mm   |
| W  | 2.6mm +/-0.15mm  |
| T  | 0.55mm +/-0.1mm  |
| B1 | 0.45mm +/-0.15mm |
| B2 | 0.5mm +/-0.2mm   |

### Packaging Specifications

|           |            |
|-----------|------------|
| Packaging | T&R, 178mm |
|-----------|------------|