



Click [here](#) for the 3D model.

#### General Information

Series	SCR Three Phase
Style	Through-Hole
Features	High Impedance, Space Saving
RoHS	Yes
Miscellaneous	87 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

#### Dimensions

D	70mm MAX
H	50mm MAX
LL	5mm +/-2mm
S	56mm NOM
Wire Size	1.7mm x 2 Parallel

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	27
Typical Component Weight	340 g

#### Specifications

Voltage AC	500 VAC
Voltage DC	500 VDC
Inductance	2 mH
Rated Current	30 A
Temperature Range	-25/+120°C
DC Resistance	4.8 mOhms