



Click [here](#) for the 3D model.

General Information

Series	SN
Style	Through-Hole
Features	Compact Size
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 30 K.
Core	Fe

Dimensions

D	25mm MAX
H	12mm MAX
LL	20mm +/-2mm
S	10mm
L2	1.5mm MAX
Wire Size	1mm

Packaging Specifications

Packaging	Bulk
Typical Component Weight	14.4 g

Specifications

Inductance	36 uH
Rated Current	5 A
Temperature Range	-40/+105°C
DC Resistance	0.02 mOhms