


 Click [here](#) for the 3D model.

General Information

Series	SN
Style	Through-Hole
Features	Compact Size
RoHS	Yes
Miscellaneous	38 (K) Temperature Rise Max.
Core	Fe

Dimensions

D	31mm MAX
H	18mm MAX
LL	20mm +/-2mm
S	16.5mm
L2	1.5mm MAX
Wire Size	1.2mm

Specifications

Inductance	143 uH
Inductance Tolerance	MIN
Rated Current	6 A
Temperature Range	-40/+105°C
DC Resistance	36 mOhms

Packaging Specifications

Packaging	Tray
Packaging Quantity	250
Typical Component Weight	38.2 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.