



Click [here](#) for the 3D model.

#### General Information

Series	SS26V
Style	Through-Hole Bobbin
RoHS	Yes
Notes	Replacement For SS28V Type And SS24V Type.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

#### Dimensions

L	26mm +/-1mm
T	20.5mm +/-1mm
H	30.5mm +/-1mm
S	10mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.55mm
F	0.8mm NOM

#### Specifications

Voltage AC	250 VAC
Inductance	9.2 mH
Rated Current	1.8 A
Temperature Range	-40/+120°C
DC Resistance	0.3 Ohms

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	350
Typical Component Weight	24.3 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.