
SS30V-R180190

Aliases (UAL30VR1801900)

Common Mode Chokes - Power, KEMET, SS30V, Through-Hole Bobbin, Common Mode, 0.019 H



General Information	
Series	SS30V
Style	Through-Hole Bobbin
RoHS	Yes
Notes	Replacement For SS35V Type And SS28V Type.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Click here for the 3D model.

Dimensions	
L	31mm +/-1mm
T	22.5mm +/-1mm
H	33mm +/-1mm
S	19.5mm +/-0.5mm
S1	11mm +/-0.5mm
Wire Size	0.6mm
F	0.8mm NOM

Specifications	
Voltage AC	250 VAC
Inductance	19 mH
Rated Current	1.8 A
Temperature Range	-40/+120°C
DC Resistance	0.23 Ohms

Packaging Specifications	
Packaging	Tray
Packaging Quantity	200
Typical Component Weight	35.2 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO