
SSB11V-R15060

Aliases (UALB11VR150600)

Common Mode Chokes - Power, KEMET, SSB11V, Through-Hole Bobbin, Common Mode, 6,000 uH



Click here for the 3D model.

General Information	
Series	SSB11V
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

Dimensions	
L	22mm +/-1mm
T	14.5mm +/-1mm
H	21.5mm +/-1mm
LL	3.5mm +/-1mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.45mm

Specifications	
Voltage AC	250 VAC
Inductance	6 mH
Rated Current	1.5 A
Temperature Range	-25/+130°C
DC Resistance	0.3 Ohms

Packaging Specifications	
Packaging	Tray
Typical Component Weight	11 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO