
SSR21H-15083

Aliases (UALR21H1508300)

Not for New Design

Common Mode Chokes - Power, KEMET, SSR21H, Through-Hole Bobbin, Common Mode, 8,300 uH



General Information	
Series	SSR21H
Style	Through-Hole Bobbin
RoHS	Yes

Dimensions	
L	23mm MAX
T	23mm MAX
H	14.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm
S1	18.5mm +/-0.5mm
Wire Size	0.45mm
F	0.8mm NOM

Specifications	
Voltage AC	250 VAC
Inductance	8300 uH
Rated Current	1.5 A
Temperature Range	-25/+120°C
DC Resistance	0.16 Ohms

Packaging Specifications	
Typical Component Weight	14 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO