



Click [here](#) for the 3D model.

General Information

| | |
|---------------|---|
| Series | SSRH24NV/NH |
| Style | Through-Hole Bobbin |
| Features | Compact Size, Light Weight, Low Rdc, Ultra-High Impedance |
| RoHS | Yes |
| Miscellaneous | 65 (K) Temperature Rise Max. |
| Core | Mn-Zn Ferrite |

Dimensions

| | |
|-----------|----------------|
| L | 25.5mm MAX |
| T | 25.5mm MAX |
| H | 18mm MAX |
| LL | 3.5mm +/-0.5mm |
| S | 13mm NOM |
| S1 | 21mm NOM |
| Wire Size | 0.7mm |
| F | 0.8mm NOM |

Packaging Specifications

| | |
|--------------------------|--------|
| Packaging | Tray |
| Packaging Quantity | 300 |
| Typical Component Weight | 22.5 g |

Specifications

| | |
|-------------------|------------|
| Voltage AC | 250 VAC |
| Inductance | 5.9 mH |
| Rated Current | 4.5 A |
| Temperature Range | -40/+120°C |
| DC Resistance | 0.048 Ohms |