



## SU9HF-03060

Aliases (UALSU9HF030600)

Common Mode Chokes - Power, KEMET, SU-9HF, Through-Hole Bobbin, Common Mode, 6,000 uH



Click [here](#) for the 3D model.

### General Information

Series	SU-9HF
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

### Dimensions

L	17mm MAX
T	15.5mm MAX
H	12mm MAX
LL	3mm MIN
S	8mm +/-0.5mm
S1	7mm +/-0.5mm
Wire Size	0.15mm
F	0.6mm NOM

### Packaging Specifications

Packaging	Tray
Packaging Quantity	1000
Typical Component Weight	3.2 g

### Specifications

Voltage AC	250 VAC
Inductance	6000 uH
Rated Current	300 mA
Temperature Range	-25/+120°C
DC Resistance	2 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.