


USEQGCQAC82H00

Aliases (USEQGCQAC82H00)

Obsolete

KEMET, QGC, Gas Detection, TO39, Infrared, Fast, Wide Operating Frequency Range, Analog Output, Integrated op amp



Click [here](#) for the 3D model.

General Information

| | |
|----------------|--|
| Series | QGC |
| Type | Gas Detection |
| Style | TO39 |
| Description | Analog output gas sensor |
| Features | Fast, Wide Operating Frequency Range, Analog Output, Integrated op amp |
| RoHS | With Exemptions |
| REACH | SVHC (PZT - CAS 12626-81-2) |
| SCIP Number | 9074c9fd-06c9-4bc8-bb2f-04f9793401ba |
| Qualifications | REACH |

Dimensions

| | |
|---|------------------|
| L | 9.15mm +/-0.05mm |
| W | 9.15mm +/-0.05mm |
| H | 19.5mm +/-0.75mm |
| T | 6.05mm NOM |

Packaging Specifications

| | |
|--------------------------|--------|
| Packaging | Bulk |
| Typical Component Weight | 1.15 g |

Specifications

| | |
|----------------------|-------------|
| Temperature Range | -40/+85°C |
| Power Supply Voltage | 2.7 - 5.0 V |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.