
USEQMSK1220900

Aliases (USEQMSK1220900)

Obsolete

KEMET, QMSM, Motion Detection, SMD, Infrared, Small SMD Package, 12C Communication Compatible, High Dynamic Range



General Information	
Series	QMSM
Type	Motion Detection
Style	SMD
Description	Evaluation Kit
Features	Small SMD Package, 12C Communication Compatible, High Dynamic Range
RoHS	With Exemptions
REACH	SVHC (PZT – CAS 12626-81-2)
SCIP Number	4bbe8810-62a4-426f-9a2e-98d9d0d9acfe
Qualifications	REACH
MSL	3

Dimensions

Packaging Specifications	
Packaging	Bulk
Typical Component Weight	300 g

Specifications	
Temperature Range	-40/+85°C
Power Supply Voltage	1.75 - 3.6 V
Current	1 - 23 uA (Supply Current, Typical)
Time Constant	10ms (10-20 Hz peak)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO