



Click [here](#) for the 3D model.

General Information	
Series	VRR Indust X7R HVHT200C
Style	Radial
Description	Commercial, High Temperature, HighVoltage
Features	Commercial
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
SCIP Number	d1f8aba3-2564-4904-a1cf-714fe85ef1ab
Termination	Gold
Lead	Wire Leads
Failure Rate	N/A
Testing and Reliability	Standard

Dimensions	
L	8.89mm MAX
W	10.16mm MAX
T	6.98mm MAX
S	6.35mm +/-0.76mm
LL	31.75mm MIN
F	0.635mm +/-0.051mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	1

Specifications	
Capacitance	1,200 pF
Tolerance	10%
Voltage DC	2000 VDC
Dielectric Withstanding Voltage	3,000 VDC
Temperature Range	-55/+200°C
Temp. Coefficient	X7R
Dissipation Factor	2.5% 1 kHz 1.0Vrms
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.