


VU-215F

Aliases (UNFVU215FXXXXX)

Obsolete

EMI Filters, KEMET, VU, Metal Cylinder, Noise Suppression



Click [here](#) for the 3D model.

General Information

Series	VU
Style	Metal Cylinder
Description	Noise Filters
RoHS	With Exemptions
Qualifications	UL, CSA
Miscellaneous	40 K Self-Temperature Rise Max.
Lead	Fast On
Terminal Type	Faston

Dimensions

D	38mm NOM
L	50mm NOM
L1	12mm NOM
L2	13mm NOM
Lead	Fast On

Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	30
Typical Component Weight	130 g

Specifications

Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	15 A (AC/DC)
Ripple Current	15 A (AC/DC)
Temperature Range	-25/+55°C
Leakage Current	1 mA
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.