




Click [here](#) for the 3D model.

General Information

Supplier	YAGEO
Series	YC
Style	SMD Network/Array
Technology	Commercial Grade
Chip Size	1206
Description	Standard Thick Film Network/Array Resistors-Convex
RoHS	Yes
Termination	Tin
AEC-Q200	No

Specifications

Resistance	10 kOhms
Resistance Tolerance	5%
Power	0.125 W (70C)
Temp. Coefficient	-/+200 ppm/C
Temperature Range	-55/ +155°C
Voltage DC	200 V (Max Continuous Voltage at Full Rated Power)
Voltage DC	200 V

Dimensions

L	5.08mm +/-0.2mm
W	3.2mm +/-0.2mm
T	0.6mm +/-0.1mm

Packaging Specifications

Packaging	T&R, 178mm
-----------	------------