



General Information

Series	H540 S
Style	Wired
Temperature Coefficient	3850 ppm/K
RoHS	Yes
Lead Type	Pt
Connection Technology	Welding, Brazing

Dimensions

L	5.2mm +/-0.2mm
W	3.9mm +/-0.2mm
W2	0.85mm +/-0.2mm
H	1mm +/-0.3mm
LL	6mm +/-1mm
Lo	0.25mm +/-0.02mm

Packaging Specifications

Packaging	Slide Blister
-----------	---------------

Specifications

Nominal Resistance R_0 [Ω]	Pt12 Ohms
Tolerance Class	+/-0.5 Ohm at OC
Temperature Range	-25/+850°C
Tolerance Temperature Minimum	-25
Tolerance Temperature Maximum	800
Maximum Heating Current	1000 mA
Maximum Heating Voltage	24 V
Peak Load	1 Hour at 850C
Heating Time	12 Sec from 25C to 700C

The information provided in this data sheet describes certain technical characteristics of the product, but shall not be qualified or construed as quality guarantee (Beschaffenheitsgarantie) in the meaning of sections 443 and 444 German Civil Code. The information provided in this data sheet regarding measurement values (including, but not limited to, response time, long-term stability, vibration and shock resistance, insulation resistance and self-heating) are average values that have been obtained under laboratory conditions in tests of large numbers of the product. Product results or measurements achieved by customer or any other person in any production, test, or other environment may vary depending on the specific conditions of use. YAGEO Nexensos does not recommend the use of standard catalogue products or automotive grades for aerospace applications or manned space flight. The customer is solely responsible to determine whether the product is suited for the customer's intended use; in this respect YAGEO Nexensos cannot assume any liability. The sale of any products by YAGEO Nexensos is exclusively subject to the General Terms of Sale and Delivery of YAGEO Nexensos in their current version at the time of purchase, which is available under www.yageo-nexensos.com/tc or may be furnished upon request. This data sheet is subject to changes without prior notice.