



Click [here](#) for the 3D model.

**General Information**

Series	A720
Dielectric	Polymer Aluminum
Style	SMD Chip
Description	Surface Mount, Polymer Aluminum
RoHS	Yes
Termination	Nickel Palladium Gold
Qualifications	UL94V-0
Halogen Free	Yes
Typical Component Weight	141 mg
Shelf Life	52 Weeks
MSL	3

**Dimensions**

L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	2.1mm MAX
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm

**Packaging Specifications**

Packaging	T&R, 180mm
Packaging Quantity	1000

**Specifications**

Capacitance	560 uF
Tolerance	20%
Voltage DC	2 VDC
Temperature Range	-55/+125°C
Rated Temperature	125°C
Life	3000 Hrs (125C)
Dissipation Factor	6% 120Hz 25C
ESR	3 mOhms (100kHz 25C)
Ripple Current	11690 mA (rms 100kHz)
Leakage Current	67.2 uA (5min 25°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.