



Click [here](#) for the 3D model.

General Information

Series	A758
Dielectric	Polymer Aluminum
Description	Single Ended, Polymer Aluminum
RoHS	Yes
Lead	Wire Leads
Halogen Free	Yes

Dimensions

D	6.3mm +/-0.5mm
L	8mm +/-1mm
S	2.5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	19mm MIN
F	0.5mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	1000

Specifications

Capacitance	330 uF
Tolerance	20%
Voltage DC	4 VDC, 4.6 VDC (Surge)
Temperature Range	-55/+105°C
Rated Temperature	105°C
Life	5000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor	10% 120Hz 20C
ESR	18 mOhms (100kHz 20C)
Ripple Current	3100 mAmps (100kHz 105C)
Leakage Current	198 uA (2min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.