



Click [here](#) for the 3D model.

General Information

Series	A785
Dielectric	Hybrid Polymer
Style	SMD Can
Description	Surface Mount, Hybrid Aluminum Polymer
RoHS	Yes
Qualifications	AEC-Q200
Halogen Free	Yes
Shelf Life	52 Weeks
MSL	1

Dimensions	
D	10mm +/-0.5mm
L	12.4mm +/-0.5mm
W	10.3mm +/-0.2mm
H	10.8mm +/-0.2mm
C	11.2mm +/-0.2mm
J	4.4mm NOM
K	3.2mm NOM
P	4.6mm NOM
R	0.7 - 1.1mm

Packaging Specifications	
Packaging	T&R, 380mm
Packaging Quantity	400

Specifications	
Capacitance	560 uF
Tolerance	20%
Voltage DC	25 VDC, 28.75 VDC (Surge)
Temperature Range	-55/+150°C
Rated Temperature	150°C
Life	1000 Hrs
Dissipation Factor	14% 120Hz 20C
ESR	17 mOhms (100kHz 20C)
Ripple Current	4000 mAmps (100kHz 125C), 2200 mAmps (100kHz 135C), 1700 mAmps (100kHz 150C)
High Temperature Solder	Yes
Leakage Current	140 uA (2min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.