



Click [here](#) for the 3D model.

General Information

| | |
|----------------|---------------------------------|
| Series | A786 |
| Dielectric | Hybrid Polymer |
| Style | SMD Can |
| Description | Surface Mount, Polymer Aluminum |
| RoHS | Yes |
| Lead | V-Chip |
| Qualifications | AEC-Q200 |
| AEC-Q200 | Yes |
| Halogen Free | Yes |
| Shelf Life | 52 Weeks |
| MSL | 1 |

Specifications

| | |
|-------------------------|---|
| Capacitance | 100 uF |
| Tolerance | 20% |
| Voltage DC | 63 VDC, 72.45 VDC (Surge) |
| Temperature Range | -55/+135°C |
| Rated Temperature | 135°C |
| Life | 1000 Hrs |
| Dissipation Factor | 8% 120Hz 20C |
| ESR | 15 mOhms (100kHz 20C) |
| Ripple Current | 4500 mAmps (100kHz 125C), 3550 mAmps (100kHz 135C) |
| High Temperature Solder | Yes |
| Leakage Current | 63 uA (2min 20°C) |

Dimensions

| | |
|---|-----------------|
| D | 10mm +/-0.5mm |
| L | 12.2mm +/-0.5mm |
| W | 10.3mm +/-0.2mm |
| H | 10.3mm +/-0.2mm |
| C | 11mm +/-0.2mm |
| P | 4.6mm NOM |
| R | 0.8 - 1.1mm |

Packaging Specifications

| | |
|--------------------|------------|
| Packaging | T&R, 380mm |
| Packaging Quantity | 400 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.