



Click [here](#) for the 3D model.

General Information

Supplier	YAGEO
Series	AC
Style	SMD Chip
Description	Automotive Grade, Thick Film Resistors
RoHS	Yes
Termination	Tin
Lead	Wrap Around, 3-Sided
Qualifications	AEC-Q200
Case Code (EIA / mm)	0402 / 1005

Dimensions

L	1mm +/-0.05mm
W	0.5mm +/-0.05mm
T	0.32mm +/-0.05mm
B1	0.2mm +/-0.1mm
B2	0.25mm +/-0.1mm

Packaging Specifications

Packaging	T&R, 178mm
Packaging Quantity	10000

Specifications

Resistance	39 Ohms
Resistance Tolerance	1%
Power	0.063 W (70C)
Temp. Coefficient	-/+100 ppm/C
Temperature Range	-55/+155°C
Voltage DC	50 V (Max Continuous Voltage at Full Rated Power), 100 Max Over Voltage, 100 Dielectric Withstanding Voltage

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.