


ALS33A152KJA450

Not for New Design

ALS33, Aluminum, Aluminum Electrolytic, 1,500 uF, 20%, 450 VDC, -40/+85°C, 22.2 mm



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--|
| Series | ALS33 |
| Dielectric | Aluminum Electrolytic |
| Description | Screw Terminal, Aluminum Electrolytic |
| RoHS | Yes |
| Lead | Oval Threaded Inserts M5 |
| Mounting | Through-Hole |
| Optional Mounting | Stud |
| Typical Component Weight | 340 g |
| Notes | Add 0.4mm To D (1.1mm When D = 88.9) And 1.1mm To L For Sleeving. MS (MxH) = M12x16. |

Dimensions

| | |
|----|------------------|
| D | 50.8mm +/-0.8mm |
| L | 114.3mm +/-1.6mm |
| T | 5.5mm +/-0.5mm |
| S | 22.2mm +/-0.5mm |
| DT | 13mm +/-0.5mm |
| LT | 119mm +/-1mm |
| TD | 10mm MIN |
| V | 13.7mm NOM |
| Z | 10mm NOM |

Packaging Specifications

| | |
|-----------|-----------|
| Packaging | Bulk, Box |
|-----------|-----------|

Specifications

| | |
|-------------------|---|
| Capacitance | 1,500 uF |
| Tolerance | 20% |
| Voltage DC | 450 VDC, 495 VDC (Surge) |
| Temperature Range | -40/+85°C |
| Rated Temperature | 85°C |
| Life | 18000 Hrs (Rated Voltage And Ripple Current At 85C), 36000 Hrs (Rated Voltage at 85C) |
| ESR | 75 mOhms (120Hz 25C), 45 mOhms (20kHz 25C) |
| Ripple Current | 8.1 Amps (120Hz 85C), 14.5 Amps (20kHz 85C) |
| Leakage Current | 4050 uA (5min 20°C) |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.