



ALT22A223DDO40

Not for New Design

ALT22, Aluminum, Aluminum Electrolytic, 22,000 uF, 20%, 40 VDC, -40/+85°C, 10 mm



General Information

Series	ALT22
Dielectric	Aluminum Electrolytic
Description	Solder Tag, Aluminum Electrolytic
RoHS	Yes
Lead	2 Flying Leads Solder Tags
Typical Component Weight	95 g
Notes	Dimensions D And L Include Slewing.

Click [here](#) for the 3D model.

Dimensions

D	40mm +/-1mm
L	55mm +/-2mm
S	10mm +/-0.1mm
LL	10mm +/-0.5mm

Packaging Specifications

Slewing	Yes
Packaging	Tray

Specifications

Capacitance	22,000 uF
Tolerance	20%
Voltage DC	40 VDC, 46 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	26000 Hrs
Leakage Current	5280 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.