



## ALT22A472AB040

Not for New Design

ALT22, Aluminum, Aluminum Electrolytic, 4,700 uF, 20%, 40 VDC, -40/+85°C, 10 mm



### General Information

Series	ALT22
Dielectric	Aluminum Electrolytic
Description	Solder Tag, Aluminum Electrolytic
RoHS	Yes
Lead	2 Flying Leads Solder Tags
Typical Component Weight	39 g
Notes	Dimensions D And L Include Slewing.

Click [here](#) for the 3D model.

### Dimensions

D	25mm +/-1mm
L	45mm +/-2mm
S	10mm +/-0.1mm
LL	10mm +/-0.5mm

### Packaging Specifications

Slewing	Yes
Packaging	Tray

### Specifications

Capacitance	4,700 uF
Tolerance	20%
Voltage DC	40 VDC, 46 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	12000 Hrs
Leakage Current	1128 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.