
ALT22A472DD100

Not for New Design

ALT22, Aluminum Electrolytic, 4,700 uF, 20%, 100 VDC, -40/+85°C, 10 mm



General Information	
Series	ALT22
Dielectric	Aluminum Electrolytic
Description	Solder Tag, Aluminum Electrolytic
Features	Solder Tag
RoHS	Yes
Lead	2 Flying Leads Solder Tags
Typical Component Weight	95 g
Notes	Dimensions D And L Include Sleeving.

Click here for the 3D model.

Dimensions	
D	40mm +/-1mm
L	55mm +/-2mm
S	10mm +/-0.1mm
LL	10mm +/-0.5mm

Packaging Specifications	
Sleeving	Yes
Packaging	Tray

Specifications	
Capacitance	4,700 uF
Tolerance	20%
Voltage DC	100 VDC, 115 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	26000 Hrs
Leakage Current	2820 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO