

## C1206C393K1RALTU

Aliases (C1206C393K1RAL7800)

SMD Comm X7R SnPb, Ceramic, 0.039 uF, 10%, 100 VDC, X7R, SMD, MLCC, Temperature Stable, SnPb Termination, 1.5 mm, 1206 / 3216



Click [here](#) for the 3D model.

### General Information

|                          |  |
|--------------------------|--|
| Series                   | SMD Comm X7R SnPb  |
| Style                    | SMD Chip   |
| Description              | SMD, MLCC, Temperature Stable, SnPb Termination  |
| Features                 | SnPb Termination   |
| RoHS                     | No   |
| Prop 65                  | <b>WARNING:</b> Cancer and reproductive harm - <a href="https://www.p65warnings.ca.gov/">https://www.p65warnings.ca.gov/</a> |
| Termination              | Lead (SnPb)  |
| Marking                  | No   |
| Typical Component Weight | 25 mg  |
| Shelf Life               | 78 Weeks   |
| MSL                      | 1  |

### Dimensions

|                      |                 |
|----------------------|-----------------|
| L                    | 3.2mm +/-0.2mm  |
| W                    | 1.6mm +/-0.2mm  |
| T                    | 0.9mm +/-0.10mm |
| S                    | 1.5mm MIN       |
| B                    | 0.5mm +/-0.25mm |
| Case Code (EIA / mm) | 1206 / 3216     |

### Packaging Specifications

|                    |                          |
|--------------------|--------------------------|
| Packaging          | T&R, 180mm, Plastic Tape |
| Packaging Quantity | 4000                     |

### Specifications

|  |   |
|--|---|
| Capacitance  | 0.039 uF  |
| Measurement Condition  | 1 kHz 1.0Vrms                                   |
| Tolerance  | 10%   |
| Voltage DC   | 100 VDC   |
| Dielectric Withstanding Voltage                                    | 250 VDC   |
| Temperature Range  | -55/+125°C                                      |
| Temp. Coefficient  | X7R   |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 15%, 1kHz 1.0Vrms                               |
| Dissipation Factor   | 2.5% 1 kHz 1.0Vrms                              |
| Aging Rate   | 3% Loss/Decade Hour: Referee Time is 1000 Hours |
| Insulation Resistance  | 25.641 GOhms                                    |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.