

## C1206S102JDGACAUTO

SMD Auto COG HV FE, Ceramic, 1,000 pF, 5%, 1,000 VDC, COG, SMD, MLCC, FE-CAP, Floating Electrode, High Voltage, Automotive Grade, 1206 / 3216



Click [here](#) for the 3D model.

### General Information

|                          |                                                                       |
|--------------------------|-----------------------------------------------------------------------|
| Series                   | SMD Auto COG HV FE                                                    |
| Style                    | SMD Chip                                                              |
| Description              | SMD, MLCC, FE-CAP, Floating Electrode, High Voltage, Automotive Grade |
| Features                 | FE-CAP, Floating Electrode, High Voltage, Automotive Grade            |
| RoHS                     | Yes                                                                   |
| Termination              | Tin                                                                   |
| Marking                  | No                                                                    |
| Qualifications           | AEC-Q200                                                              |
| Typical Component Weight | 36 mg                                                                 |
| Shelf Life               | 78 Weeks                                                              |
| MSL                      | 1                                                                     |

### Specifications

|                                                                    |                        |
|--------------------------------------------------------------------|------------------------|
| Capacitance                                                        | 1,000 pF               |
| Measurement Condition                                              | 1 MHz 1.0Vrms          |
| Tolerance                                                          | 5%                     |
| Voltage DC                                                         | 1000 VDC               |
| Dielectric Withstanding Voltage                                    | 1,200 VDC              |
| Temperature Range                                                  | -55/+125°C             |
| Temp. Coefficient                                                  | COG                    |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 30 ppm/C, 1MHz 1.0Vrms |
| Dissipation Factor                                                 | 0.1% 1 MHz 1.0Vrms     |
| Aging Rate                                                         | 0% Loss/Decade Hour    |
| Insulation Resistance                                              | 100 GOhms              |

### Dimensions

|                      |                 |
|----------------------|-----------------|
| L                    | 3.2mm +/-0.2mm  |
| W                    | 1.6mm +/-0.2mm  |
| T                    | 1.6mm +/-0.15mm |
| S                    | 1.5mm MIN       |
| B                    | 0.5mm +/-0.25mm |
| Case Code (EIA / mm) | 1206 / 3216     |

### Packaging Specifications

|                    |                          |
|--------------------|--------------------------|
| Packaging          | T&R, 180mm, Plastic Tape |
| Packaging Quantity | 2000                     |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.