C1210C475K3N1CAUTO


KPS SMD Auto X8L HT150C, Ceramic, 4.7 uF, 10%, 25 VDC, X8L

TOP VIEW

Single or Double Chip Stack

PROFILE VIEW

Single Chip Stack



Click here for the 3D model.

General Information	
Series	KPS SMD Auto X8L HT150C
Style	Stacked Chip
Description	SMD, MLCC, Stacked, Single Chip, High Temperature, Automotive Grade
Features	High Temperature, Automotive Grade
RoHS	Yes
Termination	Tin
Qualifications	AEC-Q200
Typical Component Weight	160 mg
Shelf Life	78 Weeks
MSL	1

Dimensions	
L	3.5mm +/-0.3mm
W	2.6mm +/-0.3mm
T	3.35mm +/-0.10mm
B	0.8mm +/-0.15mm

Packaging Specifications	
Packaging	T&R, 180mm, Plastic Tape
Packaging Quantity	600

Specifications	
Capacitance	4.7 uF
Measurement Condition	1 kHz 1.0Vrms
Tolerance	10%
Voltage DC	25 VDC
Dielectric Withstanding Voltage	62.5 VDC
Temperature Range	-55/+150°C
Temp. Coefficient	X8L
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	+15% (-55C to +125C), +15/-40% (125C to 150C), 1kHz 1.0Vrms
Dissipation Factor	2.5% 1 kHz 1.0Vrms
Aging Rate	3% Loss/Decade Hour: Referee Time is 1000 Hours
Insulation Resistance	106.4 MOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

© 2006 - 2026 YAGEO