



Click [here](#) for the 3D model.

General Information

Series	C44P-T
Dielectric	Metallized Polypropylene
Style	Can
Features	Single Phase PFC
RoHS	With Exemptions
Lead	Threaded Studs M10
Qualifications	UL810A approved - E107629
Mounting Details	Preferred with flexible connections for proper safety device activation (*)

Notes
 (*) Care should be taken to ensure that there still is electrical clearance of 15mm between terminations and other live or earthed parts above the capacitor, in case of safety device activation.

Dimensions

D	95mm +/-0.5mm
L	247mm +/-2mm
W	21mm +/-1mm
S	35mm +/-1mm
W1	45mm +/-1mm

Packaging Specifications

Terminal Type	Bolt - M12x16
Packaging	Carton Box
Packaging Quantity	4

Specifications

Capacitance	75 uF
Tolerance	10%
Voltage DC	2000 VDC, 2700 VDC (Surge)
Voltage AC	850 VAC
Temperature Range	-30/+70°C
Maximum Temperature Hot-Spot	+90 degrees Celsius
Rated Temperature	70°C
Max dV/dt	80 V/us
ESR	1.4 mOhms
Ripple Current	60 Amps
Inductance	180 nH
Irms	60 A
Max Power Loss	8.8 W
Thermal Resistance (Rth)	4 C/W
Rs	1.4 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.