
# C4AF7BW5100A3OK

Not for New Design

C4AF, Film, Metallized Polypropylene, Power, 10 uF, 10%, 700 VDC, 350 VAC, 85°C, 37.5 mm




Click here for the 3D model.

| General Information | |
|---|---|
| Series | C4AF |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | Harsh Environmental Conditions |
| RoHS | Yes |
| Lead | 4 Wire Leads |
| Qualifications | AEC-Q200, IEC61071, EN61071, VDE0560 |
| Typical Component Weight | 97.2 g |
| Miscellaneous | Rth = 13 C/W. |

| Dimensions | |
|---|---|
| L | 42mm +0.6/-0.7mm |
| H | 50mm +0.2/-0.7mm |
| T | 35mm +0.4/-0.7mm |
| S | 37.5mm +/-0.4mm |
| S1 | 20.3mm +/-0.4mm |
| LL | 6mm +0/-2mm |
| F | 1.2mm +/-0.05mm |

| Packaging Specifications | |
|---|---|
| Packaging | Bulk, Box |
| Packaging Quantity | 30 |

| Specifications | |
|---|---|
| Capacitance | 10 uF |
| Tolerance | 10% |
| Voltage DC | 700 VDC |
| Voltage AC | 350 VAC |
| Temperature Range | -55/+105°C |
| Rated Temperature | 85°C |
| Insulation Resistance | 3 GOhms |
| Max dV/dt | 75 V/us |
| ESR | 2.2 mOhms |
| Ripple Current | 24.8 Amps Irms (MAX), 750 Amps Ipkr |
| Inductance | 14 nH (ESL) |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2026 YAGEO