

## CA0508KRX7R7BB473

CA, Ceramic, 0.047 uF, 10%, 16 VDC, X7R, SMD, MLCC, 0508







Click here for the 3D model.

General Information	
Series	CA
Style	SMD Array
Description	SMD, MLCC
Features	Temperature Stable
RoHS	Yes
Termination	Tin
Qualifications	AEC-Q200
AEC-Q200	Yes
Chip Size	0508
MSL	1

Dimensions	
L	1.25mm +/-0.15mm
W	2mm +/-0.15mm
Т	0.6mm +/-0.1mm
A	0.28mm +/-0.1mm
В	0.2mm +/-0.1mm
Р	0.5mm +/-0.1mm

Packaging Specifications	
Packaging	T&R, 178mm, Paper Tape
Packaging Quantity	4000

Specifications	
Capacitance	0.047 uF
Tolerance	10%
Voltage DC	16 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	X7R
Dissipation Factor	5%
Insulation Resistance	10.6 MOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/20/2025 © 2006 - 2025 YAGEO