



Click [here](#) for the 3D model.

General Information

| | |
|----------------------|--|
| Series | Array Auto COG Flex |
| Style | SMD Array |
| Description | SMD, MLCC, Array, Flex Termination, Automotive Grade |
| Features | Automotive Grade |
| RoHS | Yes |
| Termination | Flexible Termination |
| Qualifications | AEC-Q200 |
| MSL | 1 |
| Case Code (EIA / mm) | 0612 / 1632 |

Dimensions

| | |
|---|-----------------|
| L | 1.6mm +/-0.2mm |
| W | 3.2mm +/-0.2mm |
| T | 0.8mm +/-0.10mm |
| P | 0.8mm +/-0.10mm |

Packaging Specifications

| | |
|--------------------|------------------------|
| Packaging | T&R, 180mm, Paper Tape |
| Packaging Quantity | 4000 |

Specifications

| | |
|-----------------------|--------------------|
| Capacitance | 82 pF |
| Tolerance | 5% |
| Voltage DC | 10 VDC |
| Temperature Range | -55/+125°C |
| Temp. Coefficient | COG |
| Dissipation Factor | 0.1% 1 MHz 1.0Vrms |
| Insulation Resistance | 100 GOhms |